

VS-15-BU-DSUB-CD-MG - D-SUB contact support



1688926

<https://www.phoenixcontact.com/us/products/1688926>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

D-SUB contact carrier, shell size 2, for 15 signal contacts, type of contact socket, for crimp contacts, straight, fixing with M3 thread, for panel mounting frame VS-15-...



Commercial data

Item number	1688926
Packing unit	100 pc
Minimum order quantity	10 pc
Sales key	AB19
Product key	ABNCAB
GTIN	4017918823078
Weight per piece (including packing)	13.13 g
Weight per piece (excluding packing)	7.53 g
Customs tariff number	85366990
Country of origin	DE

1688926

<https://www.phoenixcontact.com/us/products/1688926>

Technical data

Product properties

Product type	Contact insert
Type	D-SUB
Number of positions	15
Connection profile	D-SUB
Number of slots	1
Shielded	yes

Insulation characteristics

Overvoltage category	III
Degree of pollution	2

Electrical properties

Rated voltage in acc. with IEC 61076-2-101	400 V
Rated voltage (III/3)	125 V
Rated current	5 A (at 20 °C)
Test voltage	1200 V
Transmission medium	Copper

Connection data

Connection method	Crimp connection
-------------------	------------------

Dimensions

Width	18.1 mm
Height	12.93 mm
Length	39.52 mm

Material specifications

Flammability rating according to UL 94	V0
Housing material	Metal
Housing surface material	metal-plated
Contact surface material	Gold
Contact carrier material	Glass-fiber reinforced thermoplastics, UL 94 V0

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 500
Insertion force per signal contact	≤ 3.40 N

Environmental and real-life conditions

Ambient conditions

VS-15-BU-DSUB-CD-MG - D-SUB contact support



1688926

<https://www.phoenixcontact.com/us/products/1688926>

Degree of protection	IP20
Ambient temperature (operation)	-55 °C ... 130 °C

Mounting

Mounting type	Screw mounting
---------------	----------------

VS-15-BU-DSUB-CD-MG - D-SUB contact support



1688926

<https://www.phoenixcontact.com/us/products/1688926>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1688926>



UL Recognized

Approval ID: E118976

1688926

<https://www.phoenixcontact.com/us/products/1688926>

Classifications

ECLASS

ECLASS-13.0	27440302
ECLASS-15.0	27440323

ETIM

ETIM 10.0	EC001132
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

1688926

<https://www.phoenixcontact.com/us/products/1688926>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a), 6(a)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	1245c4d9-e14f-45df-bcf5-4625b2570275

EF3.1 Climate Change

CO2e kg	0.232 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com