

VS-08-T-RJ45/IP67-SET - RJ45 connector



1689475

<https://www.phoenixcontact.com/us/products/1689475>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



RJ45 connector, design: RJ45, degree of protection: IP20, number of positions: 8, CAT5 (IEC 11801:2002), material: Plastic, connection method: Crimp connection, cable outlet: straight, color: gray

Commercial data

Item number	1689475
Packing unit	5 pc
Minimum order quantity	1 pc
Sales key	AB17
Product key	ABNNAB
GTIN	4017918887308
Weight per piece (including packing)	18.24 g
Weight per piece (excluding packing)	16.365 g
Customs tariff number	85389099
Country of origin	DE

VS-08-T-RJ45/IP67-SET - RJ45 connector



1689475

<https://www.phoenixcontact.com/us/products/1689475>

Technical data

Product properties

Product type	Data connector (cable side)
Housing type	Plastic sleeve housing
Type	RJ45
Number of positions	8
No. of cable outlets	1
Cable outlet	straight

Insulation characteristics

Overvoltage category	II
Degree of pollution	2

Electrical properties

Rated voltage (III/3)	72 V (DC)
Transmission medium	Copper
Transmission characteristics (category)	CAT5
Transmission speed	100 Mbps

Connection data

Connection technology

Connection method	Crimp connection
-------------------	------------------

Dimensions

Width	38.4 mm
Height	19.9 mm
Length	55 mm

Material specifications

Color	gray
Flammability rating according to UL 94	V0
Housing material	Plastic

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	0 °C ... 70 °C

VS-08-T-RJ45/IP67-SET - RJ45 connector



1689475

<https://www.phoenixcontact.com/us/products/1689475>

Classifications

ECLASS

ECLASS-15.0	27440114
ECLASS-13.0	27440390

ETIM

ETIM 10.0	EC002636
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

VS-08-T-RJ45/IP67-SET - RJ45 connector



1689475

<https://www.phoenixcontact.com/us/products/1689475>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol(CAS: 119-47-1)
SCIP	4f267fa5-7b77-452d-b934-b8309cfa4cfe

EF3.1 Climate Change

CO2e kg	0.427 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com