PV-MI-YC-GC-S-1,00-3-12-NA-OE - Connector

1706609

https://www.phoenixcontact.com/us/products/1706609

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



SUNCLIX micon mains connector for the plug side, 3-pos., IP67, 20 A, 600 V, trunk line: 1.0 m, incl. dust protection cap, North American version

Commercial data

Item number	1706609
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	AB05
Product key	ABLWBX
GTIN	4046356868563
Weight per piece (including packing)	314.5 g
Weight per piece (excluding packing)	314 g
Customs tariff number	85444290
Country of origin	DE

Technical data

Product properties

Number of positions	3

Electrical properties

Rated current	20 A

Material specifications

Color	black
Flammability rating according to UL 94	V0

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
	IP67
Ambient temperature (operation)	-40 °C ... 90 °C

Classifications

UNSPSC

UNSPSC 21.0	31251501

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com