

ATS-U M - Partition plate



1742990

<https://www.phoenixcontact.com/us/products/1742990>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Partition plate, width: 1 mm, height: 69.1 mm, color: gray



Your advantages

- Universal partition plate for visual separation of terminal blocks
- Can be mounted on DIN and G rails
- Separating plate also as a replacement for TS-RTK-BEN, TSS-RTK-BEN, and TS-URK-ND

Commercial data

Item number	1742990
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE01
Product key	BE1Z1X
GTIN	4067923308503
Weight per piece (including packing)	4.437 g
Weight per piece (excluding packing)	4.287 g
Customs tariff number	39269097
Country of origin	DE

ATS-U M - Partition plate

1742990

<https://www.phoenixcontact.com/us/products/1742990>



Technical data

Product properties

Product type	Partition plate
--------------	-----------------

Dimensions

Width	1 mm
Height	69.1 mm
Length	61.6 mm

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0
Static insulating material application in cold	-60 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

ATS-U M - Partition plate

1742990

<https://www.phoenixcontact.com/us/products/1742990>



Classifications

ECLASS

ECLASS-13.0	27250301
ECLASS-15.0	27250301

ETIM

ETIM 10.0	EC000886
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

ATS-U M - Partition plate



1742990
<https://www.phoenixcontact.com/us/products/1742990>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.1 Climate Change	
CO2e kg	0.031 kg CO2e

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com