

GKM 2 GY - Cable marker carrier

1750485

<https://www.phoenixcontact.com/us/products/1750485>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable marker carrier, gray (RAL 7042), unmarked, cable diameter range: 4.8 ... 11 mm, mounting type: clip on, text field height: 8 mm, text field width: 20 mm

Your advantages

- SS-ZB ..., UC-TM ... or ZB ... can be used for labeling purposes
- The conductor marker is attached directly to a conductor

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1750485 |
| Packing unit | 100 pc |
| Minimum order quantity | 100 pc |
| Sales key | BG12 |
| Product key | BG231A |
| GTIN | 4017918028282 |
| Weight per piece (including packing) | 2.66 g |
| Weight per piece (excluding packing) | 2.46 g |
| Customs tariff number | 39269097 |
| Country of origin | DE |

GKM 2 GY - Cable marker carrier



1750485

<https://www.phoenixcontact.com/us/products/1750485>

Technical data

Product properties

| | |
|--------------|-----------------|
| Product type | Marker carriers |
|--------------|-----------------|

Dimensions

| | |
|--------|-------|
| Width | 9 mm |
| Length | 20 mm |

Text field

| | |
|-------------------|-------|
| Text field width | 20 mm |
| Text field height | 8 mm |

Material specifications

| | |
|--|--------------------------------|
| Color | gray (RAL 7042) |
| Material | PA/ABS |
| Flammability rating according to UL 94 | V2 |
| Base element material | PA/ABS |
| Components | free from silicone and halogen |

Cable/line

| | |
|-------------------------|------------------|
| External cable diameter | 4.8 mm ... 11 mm |
|-------------------------|------------------|

Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------|
| Ambient temperature (operation) | -40 °C ... 80 °C |
| Recommended ambient temperature (storage/transport) | 23 °C |
| Recommended humidity (storage/transport) | 50 % |

Mounting

| | |
|---------------|---------|
| Mounting type | clip on |
|---------------|---------|

GKM 2 GY - Cable marker carrier



1750485

<https://www.phoenixcontact.com/us/products/1750485>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281105 |
| ECLASS-15.0 | 27281105 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002248 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

GKM 2 GY - Cable marker carrier



1750485

<https://www.phoenixcontact.com/us/products/1750485>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com