GKM 2 GY - Cable marker carrier

1750485

https://www.phoenixcontact.com/us/products/1750485

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable marker carrier, gray (RAL 7042), unmarked, cable diameter range: 4.8 ... 11 mm, mounting type: clip on, text field height: 8 mm, text field width: 20 mm

Your advantages

- SS-ZB ..., UC-TM ... or ZB ... can be used for labeling purposes
- The conductor marker is attached directly to a conductor

Commercial data

Item number	1750485
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BG12
Product key	BG231A
GTIN	4017918028282
Weight per piece (including packing)	2.66 g
Weight per piece (excluding packing)	2.46 g
Customs tariff number	39269097
Country of origin	DE

Technical data

Product properties

Product type	Marker carriers

Dimensions

Width	9 mm
Length	20 mm

Text field

Text field width	20 mm
Text field height	8 mm

Material specifications

Color	gray (RAL 7042)
Material	PA/ABS
Flammability rating according to UL 94	V2
Base element material	PA/ABS
Components	free from silicone and halogen

Cable/line

External cable diameter	4.8 mm ... 11 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Mounting

Mounting type	clip on

Classifications

ECLASS

ECLASS-13.0	27281105
ECLASS-15.0	27281105

ETIM

ETIM 10.0	EC002248

UNSPSC

UNSPSC 21.0	39121400

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com