

HC-B 16-AMQ - Housing

1771587

<https://www.phoenixcontact.com/us/products/1771587>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

HEAVYCON B16 panel mounting base, with double locking latch, height: 29 mm, with flat gasket



Commercial data


| | |
|--------------------------------------|--------------------------------|
| Item number | 1771587 |
| Packing unit | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | BF55 |
| Product key | AF7AAC |
| GTIN | 4017918036300 |
| Weight per piece (including packing) | 115.4 g |
| Weight per piece (excluding packing) | 115.4 g |
| Customs tariff number | 85389099 |
| Country of origin | DE |

Technical data

Product properties

| | |
|---------------------|----------------------------|
| Product type | Housing with locking latch |
| Housing type | Panel mounting base |
| Application | Standard |
| Type | B16 |
| Shielded | no |
| Pg screw connection | none |

Dimensions

| | |
|---------------------|--|
| Dimensional drawing |  |
| Width | 43 mm |
| Height | 29 mm |
| Length | 114 mm |

Installation dimensions

| | |
|-------------------------------|-------|
| Width of the assembly cutout | 35 mm |
| Length of the assembly cutout | 86 mm |

Material specifications

| | |
|--------------------------|-----------------------------|
| Seal material | NBR |
| | CR |
| Housing material | Die-cast aluminum |
| Housing surface material | Powder-coated, gray |
| Locking latch material | Stainless steel, handle: PA |

Mechanical properties

Mechanical data

| | |
|--------------|-------|
| Locking type | Latch |
|--------------|-------|

Connection data

| | |
|-------------------|----------------------------------|
| Tightening torque | 1.5 Nm ... 2 Nm (Mounting screw) |
|-------------------|----------------------------------|

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|------------------------|
| Degree of protection | IP65 (When plugged in) |
| Ambient temperature (operation) | -40 °C ... 125 °C |

HC-B 16-AMQ - Housing


1771587

<https://www.phoenixcontact.com/us/products/1771587>




Drawings

Dimensional drawing



Dimensional drawing



Mounting cutout

HC-B 16-AMQ - Housing

1771587

<https://www.phoenixcontact.com/us/products/1771587>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440202 |
| ECLASS-15.0 | 27440202 |

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31261501 |
|-------------|----------|

HC-B 16-AMQ - Housing



1771587

<https://www.phoenixcontact.com/us/products/1771587>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com