

HC-DS-PG29-T - Pressure screw



1772719

<https://www.phoenixcontact.com/us/products/1772719>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Pressure screws, with flared cable guard, clamping area 20 mm ... 27 mm, for housing with Pg29 support



Commercial data

Item number	1772719
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BF68
Product key	AF7DFX
GTIN	4017918037369
Weight per piece (including packing)	80.58 g
Weight per piece (excluding packing)	80.58 g
Customs tariff number	74199990
Country of origin	DE

HC-DS-PG29-T - Pressure screw



1772719


<https://www.phoenixcontact.com/us/products/1772719>

Technical data

Product properties

Product type	Half screw connection
--------------	-----------------------

Dimensions

Dimensional drawing	
---------------------	--

Clamping range of the strain relief clip	20.00 mm ... 27.00 mm
--	-----------------------

External dimensions

External diameter min.	30 mm
External diameter max.	22 mm

Material specifications

Material for screw connection	Brass, nickel-plated
-------------------------------	----------------------


HC-DS-PG29-T - Pressure screw

1772719

<https://www.phoenixcontact.com/us/products/1772719>



Drawings



Dimensional drawing

HC-DS-PG29-T - Pressure screw



1772719

<https://www.phoenixcontact.com/us/products/1772719>

Classifications

UNSPSC

UNSPSC 21.0

31161514

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

info@phoenixcon.com