KGG-MSTB 2,5/ 6 - Cable housing

1803905

https://www.phoenixcontact.com/us/products/1803905

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable housing, product range: KGG-MSTB 2,5, width: 30 mm

Commercial data

Item number	1803905
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AA08
Product key	AAHZDC
GTIN	4017918046057
Weight per piece (including packing)	9.15 g
Weight per piece (excluding packing)	8.89 g
Customs tariff number	39269097
Country of origin	PL

Technical data

Product properties

Product type	Cable housing
Product family	KGG-MSTB 2,5
Number of positions	6
Pitch	0 mm

Fitting of components

Partial assembly	No

Mounting

Cable clamp

Tightening torque	0.2 Nm

Material specifications

Insulating material	ABS
Insulating material group	I
CTI according to IEC 60112	600
Flammability rating according to UL 94	HB

Dimensions

Width	30 mm
Height	37 mm
Length	19 mm
Pitch	-

Notes

General	COMBICON connection plugs can be ordered separately.

Classifications

ECLASS

ECLASS-13.0	27460402
ECLASS-15.0	27460402

ETIM

ETIM 10.0	EC002943

UNSPSC

UNSPSC 21.0	39121400

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	0.049 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com