FLRP/ICV 80 - Mounting material

1808353

https://www.phoenixcontact.com/us/products/1808353

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Pair of guide rails, is inserted into the groove ICV/...G, height: 86 mm, hole diameter: 3.4 mm

Commercial data

Item number	1808353
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AA18
Product key	AARZZA
GTIN	4017918047023
Weight per piece (including packing)	13.45 g
Weight per piece (excluding packing)	12.89 g
Customs tariff number	85369010
Country of origin	DE

Technical data


Product properties

Product type	Panel-mount frame
Product family	Accessories
Number of positions	1
Pitch	0 mm

Fitting of components

Partial assembly	No

Dimensions

Dimensional drawing	
Pitch	-

Material specifications


Color (Housing)	green (RAL 6021)

Packaging specifications


Type of packaging	packed in cardboard

Drawings


Dimensional drawing




Drilling plan/solder pad geometry




Drilling plan/solder pad geometry



Drilling plan/solder pad geometry



Drilling plan/solder pad geometry



Classifications

ECLASS

ECLASS-13.0	27460405
ECLASS-15.0	27460405

ETIM

ETIM 10.0	EC002943

UNSPSC

UNSPSC 21.0	39121400

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	0.084 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com