BF-PC 4 - Mounting flange

1827570

https://www.phoenixcontact.com/us/products/1827570

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Mounting flange, is snapped onto the left and right of the headers, for screw connection with PC 4/...-STF-7.62

Commercial data

Item number	1827570
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	AA08
Product key	AAHZBA
GTIN	4017918105242
Weight per piece (including packing)	2.506 g
Weight per piece (excluding packing)	2.305 g
Customs tariff number	85389099
Country of origin	PL

Technical data

Product properties

Product type	Flange
Product family	BF BEFESTIGUNGSFLANSCHE
Number of positions	1
Pitch	0 mm

Fitting of components

Partial assembly	No

Dimensions

Width	12.3 mm
Height	7.6 mm
Length	28.9 mm
Pitch	-

Material specifications

Color (Housing)	green (RAL 6021)
Insulating material	PA
Insulating material group	I
CTI according to IEC 60112	600
Flammability rating according to UL 94	V0

Mounting

Flange

Tightening torque	0.3 Nm

Attachment on the PCB

Tightening torque	0.3 Nm
Screw	Sheet metal screw ISO 1481-ST 2,9 x 9,5 C or ISO 7049-ST 2,9 x 9,5 C

Classifications

ECLASS

ECLASS-13.0	27460405
ECLASS-15.0	27460405

ETIM

ETIM 10.0	EC002943

UNSPSC

UNSPSC 21.0	39121400

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	0.017 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com