

CK1,6-BR-0,50ST AG - Crimp contact



1884157

<https://www.phoenixcontact.com/us/products/1884157>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Rolled pin contact, taped, silver-plated, 0.14 mm² ... 0.5 mm², contact entry from left, 2000 pcs. per roll

Commercial data

Item number	1884157
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BF65
Product key	AF7AIB
GTIN	4017918163853
Weight per piece (including packing)	0.61 g
Weight per piece (excluding packing)	0.61 g
Customs tariff number	85389099
Country of origin	CZ

CK1,6-BR-0,50ST AG - Crimp contact



1884157

<https://www.phoenixcontact.com/us/products/1884157>

Technical data

Notes

General	for HC-D...R contact carriers, the quality of a crimp connection is determined by DIN EN 60352-2
Assembly note	Note on crimp connection technology: For flexible wires only. The specified conductor cross-sections refer to the nominal cross-section of the cable used. The wiring space of the crimp connection technology is designed for fine-stranded cables in accordance with VDE 0295 Class 5. Deviating cable structures (e.g., Class 1.2 and 6 or AWG cables) should be checked before use.

Product properties

Product type	Crimp contact
Contact material type	rolled

Connection data

Connection technology	
Contact connection type	Pin

Electrical properties

Rated current	10 A (Take into account the derating of the contact insert used. The rated current corresponds to the maximum possible connection cross-section.)
---------------	---

Mechanical properties

Mechanical data	
Insertion/withdrawal cycles	≥ 500

Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	-40 °C ... 125 °C

CK1,6-BR-0,50ST AG - Crimp contact


1884157

<https://www.phoenixcontact.com/us/products/1884157>



Drawings

Dimensional drawing



CK1,6-BR-0,50ST AG - Crimp contact



1884157

<https://www.phoenixcontact.com/us/products/1884157>

Classifications

ECLASS

ECLASS-13.0	27440204
ECLASS-15.0	27440204

UNSPSC

UNSPSC 21.0	39121522
-------------	----------

CK1,6-BR-0,50ST AG - Crimp contact



1884157

<https://www.phoenixcontact.com/us/products/1884157>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com