

HC-B 24-ADP-VC-4 - Adapter plate

1885842

<https://www.phoenixcontact.com/us/products/1885842>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Adapter plates 2 mm thick, for panel cutouts of HC-B 24 size, including 1.5 mm flat gasket, size 4



Commercial data

Item number	1885842
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	ABLAZD
GTIN	4017918178598
Weight per piece (including packing)	74.5 g
Weight per piece (excluding packing)	74.43 g
Customs tariff number	85472000
Country of origin	DE

HC-B 24-ADP-VC-4 - Adapter plate



1885842

<https://www.phoenixcontact.com/us/products/1885842>

Technical data

Product properties

Product type	Adapter plate
Type	VC4

Dimensions

Dimensional drawing	
Width	141 mm
Height	43 mm
Length	3.5 mm

Material specifications

Material	V2A
Seal material	NBR

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP65


HC-B 24-ADP-VC-4 - Adapter plate

1885842

<https://www.phoenixcontact.com/us/products/1885842>

Drawings

Dimensional drawing



HC-B 24-ADP-VC-4 - Adapter plate



1885842

<https://www.phoenixcontact.com/us/products/1885842>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com