VC-DSUB 9-GC-BU/BU-SET - Connector component

1886333

https://www.phoenixcontact.com/us/products/1886333

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Connector component, D-SUB, Bus, connection method: Coupling, degree of protection: IP20



ELEKTROGERÄTE RÜCKNAHME

Commercial data

Item number	1886333
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB19
Product key	ABNCBZ
GTIN	4017918876678
Weight per piece (including packing)	11.49 g
Weight per piece (excluding packing)	9.82 g
Customs tariff number	85369010
Country of origin	DE

Technical data

Product properties

Product type	Female insert
Type	D-SUB
Connection profile	D-SUB

Electrical properties

Transmission medium	Copper

Connection data

Connection technology

Connection method	Coupling

Dimensions

Width	18.2 mm
Height	31 mm
Length	12.6 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20

Classifications

ECLASS

ECLASS-13.0	27440390
ECLASS-15.0	27440325

ETIM

ETIM 10.0	EC004746

UNSPSC

UNSPSC 21.0	39121500

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	0.414 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com