

AI 0,5-10 WH-25000 - Ferrule



2100136

<https://www.phoenixcontact.com/us/products/2100136>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ferrule, Length contact range: 10 mm, sleeve length: 16 mm, color: white

Your advantages

- The ferrules with plastic sleeve are made from soft tin-plated electrolytic copper
- The insulation reliability of close connections is increased and the splicing of wires is prevented

Commercial data

Item number	2100136
Packing unit	25,000 pc
Minimum order quantity	25,000 pc
Sales key	BH34
Product key	BH3411
GTIN	4067923213142
Weight per piece (including packing)	0.087 g
Weight per piece (excluding packing)	0.087 g
Customs tariff number	85369010
Country of origin	DE

AI 0,5-10 WH-25000 - Ferrule

2100136

<https://www.phoenixcontact.com/us/products/2100136>

Technical data

Product properties

Product type	Cable end sleeve
Conductor category	stranded conductors, class 2, 5, 6 / B, C, K, M
Product property	UL certified
	Made from soft tin-plated electrolytic copper
	Correspond to the requirements of DIN 46228-4 and UL 486F in terms of size
	Plastic collar made of polypropylene
	Halogen-free
	Long/short-term temperature: +105°C/+120°C

Connection data

Conductor connection

Conductor cross-section flexible max.	0.5 mm ²
Conductor cross-section AWG max.	20
Stripping length	13 mm

Dimensions


General

Length [l1]	16 mm
Length (Stripping length)	13 mm

Sleeve

Length [l2]	10 mm
Diameter [d1]	1.1 mm
Strength [s1]	0.15 mm

Plastic collar

Diameter [d2]	2.5 mm
Strength [s2]	0.25 mm
Dimensional drawing	
Sleeve length	16 mm
Length contact range	10 mm
Maximum stripping length	13 mm
Ferrule diameter	1.1 mm
Sleeve wall thickness	0.15 mm
Insulating collar thickness	0.25 mm

AI 0,5-10 WH-25000 - Ferrule



2100136

<https://www.phoenixcontact.com/us/products/2100136>

Inner dimensions of the insulating collar	2.5 mm
---	--------

Material specifications

Color	white (RAL 9010)
Material	CU-DHP
Material Sleeve	Electrolytic copper, tin-plated (CU-DHP)
Material Plastic collar	Polypropylene
Flammability rating according to UL 94	HB
Coating	galvanically tin-plated
Surface characteristics	Tin-plated
Components	free from silicone and halogen

Mechanical properties

Technical data


Sleeve length	16 mm
---------------	-------

Standards and regulations

Design according to standard	DIN 46228-4, UL 486F-E, NFC 63-023
------------------------------	------------------------------------

Drawings

Dimensional drawing



AI 0,5-10 WH-25000 - Ferrule



2100136

<https://www.phoenixcontact.com/us/products/2100136>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2100136>



cULus Listed

Approval ID: E488001

AI 0,5-10 WH-25000 - Ferrule



2100136

<https://www.phoenixcontact.com/us/products/2100136>

Classifications

ECLASS

ECLASS-13.0	27400201
ECLASS-15.0	27400201

ETIM

ETIM 10.0	EC000005
-----------	----------

UNSPSC

UNSPSC 21.0	27121700
-------------	----------

AI 0,5-10 WH-25000 - Ferrule



2100136

<https://www.phoenixcontact.com/us/products/2100136>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com