

UMK-BE 11,25 KMGY - Base element



2199317

<https://www.phoenixcontact.com/us/products/2199317>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Electronic board base, plug-in module base element



Commercial data

Item number	2199317
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Sales key	AC13
Product key	ACHDCA
GTIN	4046356346214
Weight per piece (including packing)	4.71 g
Weight per piece (excluding packing)	4.7 g
Customs tariff number	84879090
Country of origin	PL

UMK-BE 11,25 KMGY - Base element



2199317

<https://www.phoenixcontact.com/us/products/2199317>

Technical data

Product properties

Product type	Component housing lower part
Housing type	Press-drawn section housings
Housing series	UMK
Product family	UMK BE
Ventilation openings present	no

Dimensions

Depth	15.5 mm
Length	11.25 mm

External dimensions

Profile width (external)	77 mm
--------------------------	-------

Internal dimensions

Profile width (internal)	72.2 mm
--------------------------	---------

Material specifications

Color (Housing)	light gray (RAL 7035)
Material	PA
Flammability rating according to UL 94	V2

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

UMK-BE 11,25 KMGY - Base element



2199317

<https://www.phoenixcontact.com/us/products/2199317>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2199317>



UL Recognized

Approval ID: E240868

UMK-BE 11,25 KMGY - Base element



2199317

<https://www.phoenixcontact.com/us/products/2199317>

Classifications

ECLASS

ECLASS-13.0	27190601
ECLASS-15.0	27190601

ETIM

ETIM 10.0	EC002779
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

UMK-BE 11,25 KMGY - Base element



2199317

<https://www.phoenixcontact.com/us/products/2199317>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.24 kg CO2e
---------	--------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com