

# HC-ALU 6-53,5 PROFILE 1000 - Electronics housing



2200890

<https://www.phoenixcontact.com/us/products/2200890>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Profile housing, Panel mounting (with accessories as an option), Aluminum profile, 2-piece, profile width (internal): 53.5 mm, profile width (external): 74 mm, length: 1000 mm, height: 74 mm, depth: 53.5 mm

## Your advantages

- Aluminum extruded profile
- Available in lengths from 100 mm ... 1000 mm, can be cut to any length
- Available in overall widths from 53.5 mm ... 161 mm
- Up to IP65 degree of protection
- Can be used as handheld and wall housing
- Optional EMC seals available

## Commercial data

Item number	2200890
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AC02
Product key	ACFAAA
GTIN	4046356716239
Weight per piece (including packing)	1,510 g
Weight per piece (excluding packing)	1,510 g
Customs tariff number	76042100
Country of origin	HU

# HC-ALU 6-53,5 PROFILE 1000 - Electronics housing

2200890


<https://www.phoenixcontact.com/us/products/2200890>

## Technical data

### Product properties

Product type	Lower housing part
Housing type	Profile housing
Housing series	HC-ALU
Product family	HC-ALU 6-53,5
Ventilation openings present	no

### Dimensions

Dimensional drawing	
Height	74 mm
Depth	53.5 mm
Length	1000 mm

### External dimensions

Profile width (external)	74 mm
--------------------------	-------

### Internal dimensions

Profile width (internal)	53.5 mm
--------------------------	---------

### Material specifications

Color (Housing)	graphite gray (RAL 7024)
Material	Aluminum (powder-coated)
Surface characteristics	powder coated

### Environmental and real-life conditions

#### Ambient conditions

Max. IP code to attain	IP65
Ambient temperature (operation)	-40 °C ... 85 °C

### PCB data


Number of PCB holders	7
Type of PCB mount	Slot

### Mounting


Mounting type	Panel mounting (with accessories as an option)
---------------	--

Drawings

Dimensional drawing



Dimensional drawing



Schematic view

2200890

<https://www.phoenixcontact.com/us/products/2200890>

## Classifications

### ECLASS

ECLASS-13.0	27190601
ECLASS-15.0	27190601

### ETIM

ETIM 9.0	EC002779
----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# HC-ALU 6-53,5 PROFILE 1000 - Electronics housing



2200890

<https://www.phoenixcontact.com/us/products/2200890>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)