

# UM-ALU 4-72 PROFILE 130 - Profile

2200920

<https://www.phoenixcontact.com/us/products/2200920>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Press-drawn section housings, Screw mounting, Basic profile, profile width (internal): 72 mm, profile width (external): 75 mm, length: 130 mm, depth: 29.4 mm

## Your advantages

- Aluminum extruded profile
- Variety of connection technology
- Can be mounted on the DIN rail
- Available in lengths from 42.5 mm ... 990 mm, can be cut to any length
- Available in overall widths of 75 mm and 105 mm
- EMC protection

## Commercial data

Item number	2200920
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AC14
Product key	ACHDFA
GTIN	4046356716253
Weight per piece (including packing)	105 g
Weight per piece (excluding packing)	98 g
Customs tariff number	76042990
Country of origin	DE

# UM-ALU 4-72 PROFILE 130 - Profile

2200920


<https://www.phoenixcontact.com/us/products/2200920>

## Technical data

### Product properties

Product type	Component housing lower part
Housing type	Press-drawn section housings
Housing type	Extruded profile housings
Housing series	UM-ALU
Product family	UM-ALU 4-72
Ventilation openings present	no

### Dimensions

Dimensional drawing	
Depth	29.4 mm
Depth from top edge of DIN rail	25.5 mm
Length	130 mm

### External dimensions

Profile width (external)	75 mm
--------------------------	-------

### Internal dimensions

Profile width (internal)	72 mm
--------------------------	-------

### PCB design

PCB thickness	1.44 mm ... 2 mm
---------------	------------------

### Material specifications

Color (Profile)	aluminum color
Material Profile	Aluminum (anodized)
Surface characteristics	anodized

### Environmental and real-life conditions

#### Ambient conditions

Max. IP code to attain	IP40
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C

### PCB data

Number of PCB holders	3
Type of PCB mount	Slot

# UM-ALU 4-72 PROFILE 130 - Profile



2200920

<https://www.phoenixcontact.com/us/products/2200920>

PCB surface	8421 mm <sup>2</sup> ... 8868 mm <sup>2</sup> (TOP in conjunction with side elements COVER...AL)
	8531 mm <sup>2</sup> ... 8823 mm <sup>2</sup> (BOTTOM in conjunction with side elements COVER...AL)
	8421 mm <sup>2</sup> ... 9180 mm <sup>2</sup> (TOP in conjunction with side elements COVER...PA)
	8656 mm <sup>2</sup> ... 9180 mm <sup>2</sup> (BOTTOM in conjunction with side elements COVER...PA)
Thickness of the PCB	1.44 mm ... 2 mm

## Mounting

Mounting type	Screw mounting
Mounting position	parallel to the DIN rail

## Packaging specifications

Type of packaging	packed in cardboard
Outer packaging type	Carton

# UM-ALU 4-72 PROFILE 130 - Profile




2200920

<https://www.phoenixcontact.com/us/products/2200920>

## Drawings

Dimensional drawing



# UM-ALU 4-72 PROFILE 130 - Profile

2200920

<https://www.phoenixcontact.com/us/products/2200920>



Dimensional drawing



# UM-ALU 4-72 PROFILE 130 - Profile



2200920

<https://www.phoenixcontact.com/us/products/2200920>

## Classifications

### ECLASS

ECLASS-13.0	27190601
ECLASS-15.0	27190601

### ETIM

ETIM 10.0	EC002779
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# UM-ALU 4-72 PROFILE 130 - Profile



2200920

<https://www.phoenixcontact.com/us/products/2200920>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)