

HBUS 35,6 UT BK - Housing half shell



2201156

<https://www.phoenixcontact.com/us/products/2201156>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

DIN rail housing for use in distribution boards in accordance with DIN 43880, Lower part shell, color: black (similar RAL 9005)



Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2201156 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Note | Made to order (non-returnable) |
| Sales key | AC22 |
| Product key | ACHBBA |
| GTIN | 4046356733359 |
| Weight per piece (including packing) | 1.68 g |
| Weight per piece (excluding packing) | 1.68 g |
| Customs tariff number | 85389099 |
| Country of origin | DE |

HBUS 35,6 UT BK - Housing half shell



2201156

<https://www.phoenixcontact.com/us/products/2201156>

Technical data

Product properties

| | |
|----------------|--|
| Product type | Housing half shells |
| Housing type | DIN rail housing for use in distribution boards in accordance with DIN 43880 |
| Housing series | BC |

Dimensions

| | |
|------------------|--------|
| Horizontal pitch | 2 Div. |
|------------------|--------|

Material specifications

| | |
|--|------------------|
| Color (Housing half-shell) | black (RAL 9005) |
| Material Housing half-shell | PA |
| Flammability rating according to UL 94 | V0 |

Environmental and real-life conditions

Ambient conditions

| | |
|---|--|
| Ambient temperature (operation) | -40 °C ... 105 °C (depending on power dissipation) |
| Ambient temperature (storage/transport) | -40 °C ... 55 °C |
| Ambient temperature (assembly) | -5 °C ... 100 °C |
| Relative humidity (storage/transport) | 80 % |

HBUS 35,6 UT BK - Housing half shell



2201156

<https://www.phoenixcontact.com/us/products/2201156>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2201156>



UL Recognized

Approval ID: E240868

HBUS 35,6 UT BK - Housing half shell



2201156

<https://www.phoenixcontact.com/us/products/2201156>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27190605 |
| ECLASS-15.0 | 27190605 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002779 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

HBUS 35,6 UT BK - Housing half shell



2201156

<https://www.phoenixcontact.com/us/products/2201156>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.011 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com