

# ME PLC 40 CL GY7035 - Front connection module



2201505

<https://www.phoenixcontact.com/us/products/2201505>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

DIN rail housing, Universal cover, width: 39.7 mm, height: 129.7 mm, depth: 47 mm, color: light gray (similar RAL 7035)



## Your advantages

- Tool-free mounting
- Available in 40 mm overall width
- Flammability rating V0 in accordance with UL 94
- Variety of connection technology
- Can be mounted on the DIN rail
- With DIN-rail-mountable bus connector and power connector system as an option

## Commercial data

Item number	2201505
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AC15
Product key	ACHEAZ
GTIN	4046356839730
Weight per piece (including packing)	29.2 g
Weight per piece (excluding packing)	23.27 g
Customs tariff number	85389099
Country of origin	DE

# ME PLC 40 CL GY7035 - Front connection module



2201505

<https://www.phoenixcontact.com/us/products/2201505>

## Technical data


### Notes

Assembly note	Please observe the application note in the download area.
---------------	---

### Product properties

Product type	Upper housing part
Housing type	DIN rail housing
Housing series	ME PLC
Product family	ME PLC 40
Ventilation openings present	no

### Dimensions

Dimensional drawing	
Width	39.7 mm
Height	129.7 mm
Depth	47 mm

### Material specifications

Color (Housing)	light gray (RAL 7035)
Material Housing	PC
Flammability rating according to UL 94	V0
CTI according to IEC 60112	225

### Environmental and real-life conditions

#### Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	95 %

### Mounting

Mounting type	Latching with lower housing part
---------------	----------------------------------

### Packaging specifications

# ME PLC 40 CL GY7035 - Front connection module



2201505

<https://www.phoenixcontact.com/us/products/2201505>

Type of packaging	packed in cardboard
Outer packaging type	Carton

# ME PLC 40 CL GY7035 - Front connection module


2201505

<https://www.phoenixcontact.com/us/products/2201505>



## Drawings

Dimensional drawing



# ME PLC 40 CL GY7035 - Front connection module



2201505

<https://www.phoenixcontact.com/us/products/2201505>

## Classifications

### ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

### ETIM

ETIM 10.0	EC002779
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# ME PLC 40 CL GY7035 - Front connection module



2201505

<https://www.phoenixcontact.com/us/products/2201505>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.095 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)