

ME MAX 17,5 F/SF-PL.TRANS - Insertion plate



2201648

<https://www.phoenixcontact.com/us/products/2201648>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail housing, Insertion plate, color: transparent

Your advantages

- Can be mounted on the DIN rail
- With integrated or DIN-rail-mountable bus connector as an option

Commercial data

Item number	2201648
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	ACHABA
GTIN	4046356871754
Weight per piece (including packing)	1.27 g
Weight per piece (excluding packing)	1.27 g
Customs tariff number	85389099
Country of origin	DE

ME MAX 17,5 F/SF-PL.TRANS - Insertion plate



2201648

<https://www.phoenixcontact.com/us/products/2201648>

Technical data

Product properties

Product type	Cover
Housing type	DIN rail housing
Housing series	ME-MAX
Ventilation openings present	no

Material specifications

Color	transparent
Flammability rating according to UL 94	V2
Housing material	PC

ME MAX 17,5 F/SF-PL.TRANS - Insertion plate



2201648

<https://www.phoenixcontact.com/us/products/2201648>

Classifications

UNSPSC

UNSPSC 21.0	31261501
-------------	----------

ME MAX 17,5 F/SF-PL.TRANS - Insertion plate



2201648

<https://www.phoenixcontact.com/us/products/2201648>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com