

ME MAX 67,5 DKL TRANS - Housing cover



2201936

<https://www.phoenixcontact.com/us/products/2201936>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

DIN rail housing, Cover, width: 67.8 mm, height: 75.25 mm, depth: 5.5 mm, color: transparent



Your advantages

- Easy, tool-free mounting

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2201936 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Note | Made to order (non-returnable) |
| Product key | ACHABZ |
| GTIN | 4046356939034 |
| Weight per piece (including packing) | 11.58 g |
| Weight per piece (excluding packing) | 11.6 g |
| Country of origin | DE |

ME MAX 67,5 DKL TRANS - Housing cover



2201936

<https://www.phoenixcontact.com/us/products/2201936>

Technical data

Notes

| | |
|---------------|---|
| Assembly note | Please observe the application note in the download area. |
|---------------|---|

Product properties

| | |
|------------------------------|------------------|
| Product type | Cover |
| Housing type | DIN rail housing |
| Housing type | Modular housings |
| Housing series | ME-MAX |
| Product family | ME MAX 67,5.. |
| Ventilation openings present | no |

Dimensions

| | |
|--------|----------|
| Width | 67.8 mm |
| Height | 75.25 mm |
| Depth | 5.5 mm |

Material specifications

| | |
|--|-------------|
| Color (Housing cover) | transparent |
| Material | PC |
| Flammability rating according to UL 94 | V2 |
| CTI according to IEC 60112 | 250 |

PCB data

| | |
|-------------------|----------|
| Type of PCB mount | Latching |
|-------------------|----------|

Mounting

| | |
|---------------|----------------------------------|
| Mounting type | Latching with lower housing part |
|---------------|----------------------------------|

ME MAX 67,5 DKL TRANS - Housing cover



2201936

<https://www.phoenixcontact.com/us/products/2201936>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2201936>



UL Recognized

Approval ID: E240868

ME MAX 67,5 DKL TRANS - Housing cover



2201936

<https://www.phoenixcontact.com/us/products/2201936>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27190605 |
| ECLASS-15.0 | 27190605 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002779 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

ME MAX 67,5 DKL TRANS - Housing cover



2201936

<https://www.phoenixcontact.com/us/products/2201936>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.087 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com