

HC-ALU 6-100,5 PROFIL 40 - Electronics housing



2202073

<https://www.phoenixcontact.com/us/products/2202073>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Profile housing, Panel mounting (with accessories as an option), Aluminum profile, 2-piece, profile width (internal): 100.5 mm, profile width (external): 121 mm, length: 40 mm, height: 121 mm, depth: 32.8 mm

Your advantages

- Aluminum extruded profile
- Can be used as handheld and wall housing
- Up to IP65 degree of protection
- Optional EMC seals available

Commercial data


Item number	2202073
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	ACFAAA
GTIN	4046356987707
Weight per piece (including packing)	88.4 g
Weight per piece (excluding packing)	88.4 g
Country of origin	HU

Technical data

Product properties

Product type	Lower housing part
Housing type	Profile housing
Housing series	HC-ALU
Product family	HC-ALU 6-100,5
Ventilation openings present	no

Dimensions

Dimensional drawing	
Height	121 mm
Depth	32.8 mm
Length	40 mm

External dimensions

Profile width (external)	121 mm
--------------------------	--------

Internal dimensions

Profile width (internal)	100.5 mm
--------------------------	----------

Material specifications

Color (Housing)	graphite gray (RAL 7024)
Material	Aluminum (anodized)
Surface characteristics	anodized

Environmental and real-life conditions

Ambient conditions

Max. IP code to attain	IP65
Ambient temperature (operation)	-40 °C ... 85 °C



PCB data

Number of PCB holders	7
Type of PCB mount	Slot

Mounting

Mounting type	Panel mounting (with accessories as an option)
---------------	--

Drawings



Schematic view

HC-ALU 6-100,5 PROFIL 40 - Electronics housing



2202073

<https://www.phoenixcontact.com/us/products/2202073>

Classifications

ECLASS

ECLASS-13.0	27190601
ECLASS-15.0	27190601

ETIM

ETIM 9.0	EC002779
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

HC-ALU 6-100,5 PROFIL 40 - Electronics housing



2202073

<https://www.phoenixcontact.com/us/products/2202073>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com