

# ME MAX 22,5 PLATE TRANS - Insertion plate



2202530

<https://www.phoenixcontact.com/us/products/2202530>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail housing, Insertion plate, width: 19.2 mm, height: 73.6 mm, depth: 1 mm, color: transparent

## Your advantages

- Easy, tool-free mounting
- Plastic in accordance with UL94 V0: for more rigorous flammability requirements

## Commercial data

Item number	2202530
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Product key	ACHABZ
GTIN	4055626139708
Weight per piece (including packing)	2.04 g
Weight per piece (excluding packing)	2.04 g
Country of origin	DE

# ME MAX 22,5 PLATE TRANS - Insertion plate



2202530

<https://www.phoenixcontact.com/us/products/2202530>

## Technical data

### Notes

Assembly note	Please observe the application note in the download area.
---------------	---

### Product properties

Product type	Cover
Housing type	DIN rail housing
Housing series	ME-MAX
Ventilation openings present	no

### Dimensions

Width	19.2 mm
Height	73.6 mm
Depth	1 mm

### Material specifications

Color (Insertion plate)	transparent
Flammability rating according to UL 94	V2
CTI according to IEC 60112	250
Housing material	PC

### Mounting

Mounting type	Slot
---------------	------

# ME MAX 22,5 PLATE TRANS - Insertion plate



2202530

<https://www.phoenixcontact.com/us/products/2202530>

## Classifications

### UNSPSC

UNSPSC 21.0	31261501
-------------	----------

# ME MAX 22,5 PLATE TRANS - Insertion plate



2202530

<https://www.phoenixcontact.com/us/products/2202530>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)