
BC 107,6/40 U11 HBUS DEV-PCB - PCB

2202544

https://www.phoenixcontact.com/us/products/2202544

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Printed-circuit board for the BC 107,6 DEV-KIT



Your advantages

- Hole matrix PCB for self-assembly
- Hole matrix dimension: 2.54 mm
- Easy installation

Commercial data

Item number	2202544
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AC10
Product key	ACHBAD
GTIN	4055626142418
Weight per piece (including packing)	33.3 g
Weight per piece (excluding packing)	32.5 g
Customs tariff number	85340011
Country of origin	DE

Technical data

Product properties

Product type	PCB
Housing type	DIN rail housing for use in distribution boards in accordance with DIN 43880
Housing series	BC
Product family	BC 107,6..

Dimensions

Horizontal pitch	6 HP

Material specifications

Color (Housing)	green (RAL 6021)
Housing material	FR 4-21

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	110 °C (depending on power dissipation)

Classifications

ECLASS

ECLASS-13.0	27260692
ECLASS-15.0	27260692

ETIM

ETIM 10.0	EC001031

UNSPSC

UNSPSC 21.0	31261500

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com