

# ME PLC 40 CS BK - Housing cover



2202721

<https://www.phoenixcontact.com/us/products/2202721>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

DIN rail housing, Cover, width: 39.7 mm, height: 51.8 mm, depth: 13.65 mm, color: black (similar RAL 9005)



## Your advantages

- Tool-free mounting
- Available in 40 mm overall width
- Flammability rating V0 in accordance with UL 94
- Variety of connection technology
- Can be mounted on the DIN rail
- With DIN-rail-mountable bus connector and power connector system as an option

## Commercial data

Item number	2202721
Packing unit	10 pc
Minimum order quantity	250 pc
Note	Made to order (non-returnable)
Product key	ACHEAZ
GTIN	4055626187723
Weight per piece (including packing)	6 g
Weight per piece (excluding packing)	5.92 g
Country of origin	DE

# ME PLC 40 CS BK - Housing cover



2202721

<https://www.phoenixcontact.com/us/products/2202721>

## Technical data

### Notes

Assembly note	Please observe the application note in the download area.
---------------	---

### Product properties

Product type	Upper housing part
Housing type	DIN rail housing
Housing series	ME PLC
Product family	ME PLC 40
Ventilation openings present	no

### Dimensions

Width	39.7 mm
Height	51.8 mm
Depth	13.65 mm

### Material specifications

Color (Housing cover)	black (RAL 9005)
Material	PC
Flammability rating according to UL 94	V0
CTI according to IEC 60112	225
Surface characteristics	untreated

### Environmental and real-life conditions

#### Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	95 %

### Mounting

Mounting type	Latching with lower housing part
---------------	----------------------------------

### Packaging specifications

Type of packaging	packed in cardboard
Outer packaging type	Carton

# ME PLC 40 CS BK - Housing cover



2202721

<https://www.phoenixcontact.com/us/products/2202721>

## Classifications

### ECLASS

ECLASS-13.0	27190603
ECLASS-15.0	27190603

### ETIM

ETIM 10.0	EC002779
-----------	----------

### UNSPSC

UNSPSC 21.0	31261501
-------------	----------

# ME PLC 40 CS BK - Housing cover



2202721

<https://www.phoenixcontact.com/us/products/2202721>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)