

# UM 122-PROFIL PA L12,39CM KMGY - Profile



2203013

<https://www.phoenixcontact.com/us/products/2203013>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Press-drawn section housings, Latching with side elements, latching with foot element, Basic profile, profile width (internal): 122 mm, profile width (external): 127.5 mm, length: 123.9 mm



## Commercial data

Item number	2203013
Packing unit	50 pc
Minimum order quantity	100 pc
Note	Made to order (non-returnable)
Product key	ACHDBA
GTIN	4055626298115
Weight per piece (including packing)	66.9 g
Weight per piece (excluding packing)	66.9 g
Country of origin	DE

2203013

<https://www.phoenixcontact.com/us/products/2203013>

## Technical data

### Product properties

Product type	Component housing lower part
Housing type	Press-drawn section housings
Housing type	Extruded profile housings
Housing series	UM
Product family	UM122
Ventilation openings present	no

### Dimensions

Length	123.9 mm
--------	----------

#### External dimensions

Profile width (external)	127.5 mm
--------------------------	----------

#### Internal dimensions

Profile width (internal)	122 mm
--------------------------	--------

### Material specifications

Color (Housing)	light gray (RAL 7035)
Material	PA

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

### Mounting

Mounting type	Latching with side elements, latching with foot element
---------------	---

# UM 122-PROFIL PA L12,39CM KMGY - Profile



2203013

<https://www.phoenixcontact.com/us/products/2203013>

## Classifications

### ECLASS

ECLASS-13.0	27190601
ECLASS-15.0	27190601

### ETIM

ETIM 10.0	EC002779
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# UM 122-PROFIL PA L12,39CM KMGY - Profile



2203013

<https://www.phoenixcontact.com/us/products/2203013>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)