D T 15,0 XGA L - Display

2203553

https://www.phoenixcontact.com/us/products/2203553

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



TFT module 15", 1024 x 768 pixels, transmissive/color, LED backlight, white, interface: LVDS, 8 bit, operating temperature: -20 °C ... 70 °C

Your advantages

- High-contrast TFT color display
- Easy and time-saving integration into DCS series electronics housings
- Long-term availability
- Ideal protective shield and gasket material
- High resolution with rapid response time
- Common interface for your electronics

Commercial data

Item number	2203553
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AC05
Product key	ACGAAB
GTIN	4055626482613
Weight per piece (including packing)	1,428.7 g
Weight per piece (excluding packing)	1,428.7 g
Customs tariff number	85312040
Country of origin	CN

Technical data

Product properties

Product type	Display

Display

Display type	Color display TFT
Display type	LCD with backlighting
Display type	transmissive
Panel technology	TFT
Diagonals (cm)	38.1 cm
Diagonals (inch)	15 in.
Screen resolution	1024 x 768 Pixel(s) (XGA)
Display formats	4:3
Display lighting type	LED, white
Service life, lighting appliance	50000 h
Representation	color

Interfaces

Interface	LVDS 1 port

Dimensions

Dimensions	327 mm x 254 mm x 12 mm (Mounting panel dimensions)
	304 mm x 228 mm (Active range)
	307 mm x 231 mm (Viewing area)

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 70 °C
Ambient temperature (storage/transport)	-30 °C ... 80 °C

Mounting

Mounting type	Screw mounting

Packaging specifications

Type of packaging	packed in cardboard

Classifications

ECLASS

ECLASS-15.0	27261890
ECLASS-13.0	27261890

ETIM

ETIM 10.0	EC011541

UNSPSC

UNSPSC 21.0	43211900

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com