

ECS-PM - Mounting bracket



2230013

<https://www.phoenixcontact.com/us/products/2230013>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Mounting set for mast mounting



Commercial data

Item number	2230013
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AC04
Product key	ACFDAG
GTIN	4055626461212
Weight per piece (including packing)	181.5 g
Weight per piece (excluding packing)	167.98 g
Customs tariff number	39269097
Country of origin	US

ECS-PM - Mounting bracket

2230013

<https://www.phoenixcontact.com/us/products/2230013>



Technical data

Notes

Assembly note	Please observe the application note in the download area.
---------------	---

Product properties

Product type	Mounting material
Housing type	Outdoor housing
Housing type	Outdoor housings
Housing series	ECS

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

ECS-PM - Mounting bracket

2230013

<https://www.phoenixcontact.com/us/products/2230013>



Classifications

ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

ETIM

ETIM 10.0	EC002779
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

ECS-PM - Mounting bracket



2230013

<https://www.phoenixcontact.com/us/products/2230013>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com