

# PACT MCR-V2-6315- 95-1000-5A-1 - Current transformer



2277226

<https://www.phoenixcontact.com/us/products/2277226>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Window-type current transformer, 1000 A AC primary current; 5 A AC secondary current; accuracy class 1; 10 VA rated power

## Your advantages

- Primary rated current  $I_{pn}$ : 0 ... (200 ... 2500) A
- Circular conductor dimensions:  $\varnothing$  53 mm

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 2277226                        |
| Packing unit                         | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | C444                           |
| Product key                          | CMMA11                         |
| GTIN                                 | 4046356305037                  |
| Weight per piece (including packing) | 480.1 g                        |
| Weight per piece (excluding packing) | 432.5 g                        |
| Customs tariff number                | 85043129                       |
| Country of origin                    | DE                             |

# PACT MCR-V2-6315- 95-1000-5A-1 - Current transformer



2277226

<https://www.phoenixcontact.com/us/products/2277226>

## Technical data

### Product properties

|                |                                 |
|----------------|---------------------------------|
| Product type   | Current transformer             |
| Product family | Window-type current transformer |

### Electrical properties

|                          |                                |
|--------------------------|--------------------------------|
| Rated insulation voltage | 1 kV (Phase/neutral conductor) |
|--------------------------|--------------------------------|

### General

|                   |                                 |
|-------------------|---------------------------------|
| Can be calibrated | no                              |
| Converter type    | Window-type current transformer |

### Input data

#### Current transformer

|                                  |                                 |
|----------------------------------|---------------------------------|
| Rated power                      | 10 VA                           |
| Thermal rated short-time current | $I_{th} = 60 * I_n$             |
| Thermal rated continuous current | $I_d = 1.2 * I_n$               |
| Rated surge current              | $I_{dyn} = 2.5 * I_{th}$        |
| Rated frequency $f_n$            | 50 Hz<br>60 Hz                  |
| Primary rated current $I_{pn}$   | 0 A ... 1000 A                  |
| Can be calibrated                | no                              |
| Converter type                   | Window-type current transformer |

### Output data

#### Signal

|                                  |        |
|----------------------------------|--------|
| Secondary rated current $I_{sn}$ | 5 A AC |
| Surge current limitation factor  | FS 5   |
| Accuracy class                   | 1      |

### Connection data

|                                  |  |
|----------------------------------|--|
| Connection method                | Screw connection   |
| Conductor cross-section flexible | 2x 2.5 mm <sup>2</sup> ... 4 mm <sup>2</sup> (Secondary terminals) |

### Dimensions

#### Item dimensions

|        |        |
|--------|--------|
| Width  | 30 mm  |
| Height | 121 mm |
| Depth  | 95 mm  |

#### Item dimensions with alternative mounting

|       |       |
|-------|-------|
| Width | 95 mm |
|-------|-------|

# PACT MCR-V2-6315- 95-1000-5A-1 - Current transformer



2277226

<https://www.phoenixcontact.com/us/products/2277226>

|        |        |
|--------|--------|
| Height | 121 mm |
| Depth  | 30 mm  |

## Copper rail

|        |       |
|--------|-------|
| Width  | 63 mm |
| Height | 15 mm |

## Copper rail 2

|        |       |
|--------|-------|
| Width  | 50 mm |
| Height | 10 mm |

## Copper rail 3

|        |       |
|--------|-------|
| Width  | 40 mm |
| Height | 40 mm |

## Circular conductor

|          |       |
|----------|-------|
| Diameter | 53 mm |
|----------|-------|

## Material specifications

|                  |                  |
|------------------|------------------|
| Color            | black (RAL 9005) |
| Housing material | PA 6.6           |

## Environmental and real-life conditions

### Ambient conditions

|   |                                  |
|---|----------------------------------|
| Ambient temperature (operation)         | -25 °C ... 40 °C                 |
| Ambient temperature (storage/transport) | -25 °C ... 40 °C                 |
| Permissible humidity (operation)        | Use only indoors, non-condensing |
| Insulating material class               | E                                |

## Standards and regulations

|                       |          |
|-----------------------|----------|
| Standards/regulations | EN 50178 |
|                       | EN 61869 |

## Mounting

|               |                   |
|---------------|-------------------|
| Mounting type | DIN rail mounting |
|---------------|-------------------|

# PACT MCR-V2-6315- 95-1000-5A-1 - Current transformer




2277226

<https://www.phoenixcontact.com/us/products/2277226>

## Drawings

Dimensional drawing



# PACT MCR-V2-6315- 95-1000-5A-1 - Current transformer



2277226

<https://www.phoenixcontact.com/us/products/2277226>

## Environmental product compliance

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-50<br>An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |
|--|--|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)