

PACT MCR-V2-6040- 96-1500-5A-1 - Current transformer



2277718

<https://www.phoenixcontact.com/us/products/2277718>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Window-type current transformer, 1,500 A AC primary current; 5 A AC secondary current; accuracy class 1; 10 VA rated power

Your advantages

- Primary rated current I_{pn}: 0 ... (200 ... 2000) A
- Rail dimensions: 60 x 40 mm; 50 x 50 mm

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2277718 |
| Packing unit | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | C444 |
| Product key | CMMA11 |
| GTIN | 4046356458764 |
| Weight per piece (including packing) | 386.6 g |
| Weight per piece (excluding packing) | 367.9 g |
| Customs tariff number | 85043129 |
| Country of origin | DE |

PACT MCR-V2-6040- 96-1500-5A-1 - Current transformer



2277718

<https://www.phoenixcontact.com/us/products/2277718>

Technical data

Product properties

| | |
|----------------|---------------------------------|
| Product type | Current transformer |
| Product family | Window-type current transformer |

Electrical properties

| | |
|--------------------------|--------------------------------|
| Rated insulation voltage | 1 kV (Phase/neutral conductor) |
|--------------------------|--------------------------------|

General

| | |
|-------------------|---------------------------------|
| Can be calibrated | no |
| Converter type | Window-type current transformer |

Input data

Current transformer

| | |
|----------------------------------|---------------------------------|
| Rated power | 10 VA |
| Thermal rated short-time current | $I_{th} = 60 * I_n$ |
| Thermal rated continuous current | $I_d = 1.2 * I_n$ |
| Rated surge current | $I_{dyn} = 2.5 * I_{th}$ |
| Rated frequency f_n | 50 Hz 60 Hz |
| Primary rated current I_{pn} | 0 A ... 1500 A |
| Can be calibrated | no |
| Converter type | Window-type current transformer |

Output data

Signal

| | |
|----------------------------------|--------|
| Secondary rated current I_{sn} | 5 A AC |
| Surge current limitation factor | FS 5 |
| Accuracy class | 1 |

Connection data

| | |
|----------------------------------|--|
| Connection method | Screw connection |
| Conductor cross-section flexible | 2x 2.5 mm ² ... 4 mm ² (Secondary terminals) |

Dimensions

Item dimensions

| | |
|--------|--------|
| Width | 30 mm |
| Height | 121 mm |
| Depth | 96 mm |

Item dimensions with alternative mounting

| | |
|-------|-------|
| Width | 96 mm |
|-------|-------|

PACT MCR-V2-6040- 96-1500-5A-1 - Current transformer



2277718

<https://www.phoenixcontact.com/us/products/2277718>

| | |
|--------|--------|
| Height | 121 mm |
| Depth | 30 mm |

Copper rail

| | |
|--------|-------|
| Width | 60 mm |
| Height | 40 mm |

Copper rail 2

| | |
|--------|-------|
| Width | 50 mm |
| Height | 50 mm |

Circular conductor

| | |
|----------|-------|
| Diameter | 61 mm |
|----------|-------|

Material specifications

| | |
|------------------|------------------|
| Color | black (RAL 9005) |
| Housing material | PA 6.6 |

Environmental and real-life conditions

Ambient conditions

| | |
|---|----------------------------------|
| Ambient temperature (operation) | -25 °C ... 40 °C |
| Ambient temperature (storage/transport) | -25 °C ... 40 °C |
| Permissible humidity (operation) | Use only indoors, non-condensing |
| Insulating material class | E |

Standards and regulations

| | |
|-----------------------|----------|
| Standards/regulations | EN 50178 |
| | EN 61869 |

Mounting

| | |
|---------------|-------------------|
| Mounting type | DIN rail mounting |
|---------------|-------------------|


PACT MCR-V2-6040- 96-1500-5A-1 - Current transformer



2277718

<https://www.phoenixcontact.com/us/products/2277718>

Drawings



PACT MCR-V2-6040- 96-1500-5A-1 - Current transformer



2277718

<https://www.phoenixcontact.com/us/products/2277718>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com