

ME 22,5 PLATE-MSTBO KMGY - Insertion plate



2279279

<https://www.phoenixcontact.com/us/products/2279279>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

DIN rail housing, Fitted cover for ME upper parts ME...OTP...MSTBO..., width: 20 mm, height: 54 mm, depth: 4.75 mm, color: light gray (similar RAL 7035)



Your advantages

- Easy, tool-free mounting
- Plastic in accordance with UL94 V0: for more rigorous flammability requirements

Commercial data

Item number	2279279
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AC08
Product key	ACHAAZ
GTIN	4046356299527
Weight per piece (including packing)	2.15 g
Weight per piece (excluding packing)	2.13 g
Customs tariff number	85389099
Country of origin	DE

ME 22,5 PLATE-MSTBO KMGY - Insertion plate



2279279

<https://www.phoenixcontact.com/us/products/2279279>

Technical data

Product properties

Product type	Cover
Housing type	DIN rail housing
Housing series	ME
Product family	ME 22,5..
Ventilation openings present	no

Dimensions

Width	20 mm
Height	54 mm
Depth	4.75 mm

Material specifications

Color (Insertion plate)	light gray (RAL 7035)
Material Housing	PA
Flammability rating according to UL 94	V0
CTI according to IEC 60112	600

Mounting

Mounting type	Slot
---------------	------

ME 22,5 PLATE-MSTBO KMGY - Insertion plate



2279279

<https://www.phoenixcontact.com/us/products/2279279>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2279279>



UL Recognized

Approval ID: E240868

ME 22,5 PLATE-MSTBO KMGY - Insertion plate



2279279

<https://www.phoenixcontact.com/us/products/2279279>

Classifications

ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

ETIM

ETIM 10.0	EC002779
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

ME 22,5 PLATE-MSTBO KMGY - Insertion plate



2279279

<https://www.phoenixcontact.com/us/products/2279279>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com