

FLK 26 - Termination board

2280051

<https://www.phoenixcontact.com/us/products/2280051>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows a 20-position version

VARIOFACE module, with screw connection and flat-ribbon cable connector, for mounting on NS 32 or NS 35/7.5, with male connector and short and long locking latches for sockets, 26-pos. (separate test socket for each channel)

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2280051 |
| Packing unit | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | NULL |
| Product key | DK2181 |
| GTIN | 4017918054311 |
| Weight per piece (including packing) | 127.75 g |
| Weight per piece (excluding packing) | 112.79 g |
| Customs tariff number | 85369010 |
| Country of origin | DE |

FLK 26 - Termination board



2280051

<https://www.phoenixcontact.com/us/products/2280051>

Technical data

Product properties

| | |
|---------------------|------------------|
| Product type | Interface module |
| Number of positions | 26 |

Insulation characteristics

| | |
|----------------------|----|
| Overvoltage category | II |
| Pollution degree | 2 |

Electrical properties

| | |
|---|-----------|
| Nominal voltage U_N | < 50 V AC |
| | 60 V DC |
| Max. current carrying capacity per branch | 1 A |

Connection data

PCB connection

| | |
|----------------------------------|---|
| Connection in acc. with standard | IEC / EN |
| Connection method | Screw connection |
| Stripping length | 8 mm |
| Screw thread | M3 |
| Conductor cross-section rigid | 0.2 mm ² ... 4 mm ² |
| Conductor cross-section flexible | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section AWG | 24 ... 12 |

Controller level

| | |
|---------------------|-------------------|
| Connection method | IDC/FLK pin strip |
| Number of positions | 26 |
| Pitch | 2.54 mm |

Signaling

| | |
|------------------------|----|
| Status display | no |
| Status display present | no |

Dimensions

Item dimensions

| | |
|--------|---------|
| Width | 75.5 mm |
| Height | 50 mm |
| Depth | 58.5 mm |

Material specifications

| | |
|-----------------------------|-------------------|
| Color | green (RAL 6021) |
| Housing insulation material | Polyamide 6 green |

FLK 26 - Termination board



2280051

<https://www.phoenixcontact.com/us/products/2280051>

Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------|
| Ambient temperature (operation) | -20 °C ... 50 °C |
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |

Standards and regulations

| | |
|-----------------------|--------------|
| Standards/regulations | IEC 60664 |
| | DIN EN 50178 |

Mounting

| | |
|-------------------|-------------------|
| Mounting type | DIN rail mounting |
| Mounting position | any |

Notes

| | |
|--------------------|--|
| Notes on operation | For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met. |
|--------------------|--|

FLK 26 - Termination board

2280051

<https://www.phoenixcontact.com/us/products/2280051>



Drawings

Circuit diagram



FLK 26 - Termination board

2280051

<https://www.phoenixcontact.com/us/products/2280051>



Environmental product compliance

EU REACH SVHC

| REACH candidate substance (CAS No.) | |
|-------------------------------------|--|
|-------------------------------------|--|

| | |
|--|----------------------------|
| | No substance above 0.1 wt% |
|--|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com