


FLKMS 20 - Termination board

2281555

<https://www.phoenixcontact.com/us/products/2281555>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows a 50-pos.
version

VARIOFACE module, with screw connection and flat-ribbon cable connector, for mounting on NS 32 or NS 35/7.5, with pin strip and short and long locking latches for socket strips, 20-pos.

Commercial data

Item number	2281555
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C422
Product key	DK2181
GTIN	4017918054809
Weight per piece (including packing)	148.2 g
Weight per piece (excluding packing)	1.1 g
Customs tariff number	85369010
Country of origin	DE

FLKMS 20 - Termination board



2281555

<https://www.phoenixcontact.com/us/products/2281555>

Technical data

Product properties

Product type	Interface module
Product family	VARIOFACE
Number of positions	20

Electrical properties

Nominal voltage U_N	< 50 V AC
	60 V DC
Max. current carrying capacity per branch	1 A

Connection data

Field level

Connection in acc. with standard	IEC / EN
Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12

Controller level

Connection method	IDC/FLK pin strip
Number of positions	20
Pitch	2.54 mm

Signaling

Status display present	no
------------------------	----

Dimensions

Item dimensions

Width	56.5 mm
Height	72 mm
Depth	77 mm

Material specifications

Color	green (RAL 6021)
Housing insulation material	Polyamide 6.6 green

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
---------------------------------	------------------

FLKMS 20 - Termination board



2281555

<https://www.phoenixcontact.com/us/products/2281555>

Ambient temperature (storage/transport)	-20 °C ... 70 °C
---	------------------

Standards and regulations

Standards/regulations	IEC 60664
	DIN EN 50178

Mounting

Mounting type	DIN rail mounting
Mounting position	any

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

FLKMS 20 - Termination board

2281555

<https://www.phoenixcontact.com/us/products/2281555>



Drawings

Circuit diagram



FLKMS 20 - Termination board

2281555

<https://www.phoenixcontact.com/us/products/2281555>



Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com