

FLKMS-D37 SUB/S - Termination board



2281733

<https://www.phoenixcontact.com/us/products/2281733>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Termination board, connection 1: Screw connection, connection 2: D-SUB pin strip 37-position

Commercial data

Item number	2281733
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C422
Product key	DK2182
GTIN	4017918054984
Weight per piece (including packing)	214.06 g
Weight per piece (excluding packing)	2.24 g
Customs tariff number	85369010
Country of origin	DE

FLKMS-D37 SUB/S - Termination board



2281733

<https://www.phoenixcontact.com/us/products/2281733>

Technical data

Product properties

Product type	Interface module
Product family	VARIOFACE

Electrical properties

Nominal voltage U_N	25 V AC
	50 V DC

Connection data

Field level

Connection in acc. with standard	IEC / EN
Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12

Controller level

Connection method	D-SUB pin strip
Number of positions	37

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

FLKMS-D37 SUB/S - Termination board




2281733

<https://www.phoenixcontact.com/us/products/2281733>

Drawings

Circuit diagram



Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com