

# FLKM-D50 SUB/S/LA/SO389 - Termination board



2293239

<https://www.phoenixcontact.com/us/products/2293239>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE interface module, with screw connection and D-SUB miniature pin strip, for mounting on NS 35/7.5 or NS 32, 50-pos.

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2293239       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 10 pc         |
| Product key                          | DK2A82        |
| GTIN                                 | 4017918574499 |
| Weight per piece (including packing) | 363.62 g      |
| Weight per piece (excluding packing) | 363.62 g      |
| Country of origin                    | DE            |

# FLKM-D50 SUB/S/LA/SO389 - Termination board



2293239

<https://www.phoenixcontact.com/us/products/2293239>

## Technical data

### Product properties

|              |                  |
|--------------|------------------|
| Product type | Interface module |
|--------------|------------------|

### Mounting

|               |                   |
|---------------|-------------------|
| Mounting type | DIN rail mounting |
|---------------|-------------------|

### Notes

|                    |  |
|--------------------|--|
| Notes on operation | For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met. |
|--------------------|--|

# FLKM-D50 SUB/S/LA/SO389 - Termination board



2293239

<https://www.phoenixcontact.com/us/products/2293239>

## Environmental product compliance

### China RoHS

|  |   |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50   |
|  | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)