


UM 45-FLK64/ZFKDS - Termination board



2293608

<https://www.phoenixcontact.com/us/products/2293608>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE module, with spring-cage connection and flat-ribbon cable connector, for mounting on NS 35/7.5, 64-pos.

The figure shows a 50-pos. version

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2293608 |
| Packing unit | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | NULL |
| Product key | DK21A1 |
| GTIN | 4017918120504 |
| Weight per piece (including packing) | 207.2 g |
| Weight per piece (excluding packing) | 176.87 g |
| Customs tariff number | 85369010 |
| Country of origin | DE |

UM 45-FLK64/ZFKDS - Termination board



2293608

<https://www.phoenixcontact.com/us/products/2293608>

Technical data

Product properties

| | |
|---------------------|------------------|
| Product type | Interface module |
| Number of positions | 64 |

Insulation characteristics

| | |
|----------------------|----|
| Overvoltage category | II |
| Pollution degree | 2 |

Electrical properties

| | |
|---|-----------|
| Nominal voltage U_N | < 50 V AC |
| | 60 V DC |
| Max. current carrying capacity per branch | 1 A |

Connection data

Field level

| | |
|----------------------------------|---|
| Connection in acc. with standard | IEC / EN |
| Connection method | Spring-cage connection |
| Stripping length | 8 mm |
| Conductor cross-section rigid | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section flexible | 0.2 mm ² ... 1.5 mm ² |
| Conductor cross-section AWG | 24 ... 14 |

Controller level

| | |
|-----------------------|-------------------|
| Connection method | IDC/FLK pin strip |
| Number of connections | 1 |
| Number of positions | 64 |
| Pitch | 2.54 mm |

Signaling

| | |
|------------------------|----|
| Status display | no |
| Status display present | no |

Dimensions

Item dimensions

| | |
|--------|--------|
| Width | 186 mm |
| Height | 45 mm |
| Depth | 50 mm |

Material specifications

| | |
|-----------------------------|------------------|
| Color | green (RAL 6021) |
| Housing insulation material | PVC |

UM 45-FLK64/ZFKDS - Termination board



2293608

<https://www.phoenixcontact.com/us/products/2293608>

Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------|
| Ambient temperature (operation) | -20 °C ... 50 °C |
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |

Standards and regulations

| | |
|-----------------------|--------------|
| Standards/regulations | IEC 60664 |
| | DIN EN 50178 |

Mounting

| | |
|-------------------|-------------------|
| Mounting type | DIN rail mounting |
| Mounting position | any |

Notes

| | |
|--------------------|--|
| Notes on operation | For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met. |
|--------------------|--|

UM 45-FLK64/ZFKDS - Termination board

2293608

<https://www.phoenixcontact.com/us/products/2293608>



Drawings

Circuit diagram



UM 45-FLK64/ZFKDS - Termination board



2293608

<https://www.phoenixcontact.com/us/products/2293608>

Environmental product compliance

EU REACH SVHC

| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com