


# FLKM 40/32IO/S100 - Passive module



2294377

<https://www.phoenixcontact.com/us/products/2294377>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE I/O module, 32 channels for Siemens SIMATIC® S5-95U and S5-100U

## Commercial data

Item number	2294377
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	DK218S
GTIN	4017918132736
Weight per piece (including packing)	239.8 g
Weight per piece (excluding packing)	157.28 g
Customs tariff number	85369010
Country of origin	DE

# FLKM 40/32IO/S100 - Passive module



2294377

<https://www.phoenixcontact.com/us/products/2294377>

## Technical data

### Product properties

Product type	Interface module
Number of positions	40

### Insulation characteristics

Overvoltage category	II
Pollution degree	2

### Electrical properties

Nominal voltage $U_N$	< 50 V AC
	60 V DC
Max. current carrying capacity per branch	1 A

### Connection data

#### Field level

Connection in acc. with standard	IEC / EN
Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12

#### Controller level

Connection method	IDC/FLK pin strip
Number of positions	40
Pitch	2.54 mm

### Signaling

Status display	no
Status display present	no

### Dimensions

#### Item dimensions

Width	112.5 mm
Height	90 mm
Depth	68 mm

### Material specifications

Color	green (RAL 6021)
Housing insulation material	PVC

# FLKM 40/32IO/S100 - Passive module



2294377

<https://www.phoenixcontact.com/us/products/2294377>

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
---------------------------------	------------------

## Standards and regulations

Standards/regulations	IEC 60664
	IEC 60664A
	DIN VDE 0110
	DIN VDE 0160 (in parts)

## Mounting

Mounting position	any
-------------------	-----

## Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

# FLKM 40/32IO/S100 - Passive module




2294377

<https://www.phoenixcontact.com/us/products/2294377>

## Drawings

### Circuit diagram



a = pin strip FLK 40

# FLKM 40/32IO/S100 - Passive module



2294377

<https://www.phoenixcontact.com/us/products/2294377>

## Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)