

FLK 40/50EZ-DR/ 100/OBC/SLC - Cable



2295509

<https://www.phoenixcontact.com/us/products/2295509>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Commercial data

Item number	2295509
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C421
Product key	DK221R
GTIN	4017918405663
Weight per piece (including packing)	153.4 g
Weight per piece (excluding packing)	148.4 g
Customs tariff number	85444290
Country of origin	DE

FLK 40/50EZ-DR/ 100/OBC/SLC - Cable



2295509

<https://www.phoenixcontact.com/us/products/2295509>

Technical data

Product properties

Product type	System cable
--------------	--------------

Cable/line

Cable length	1 m
--------------	-----

40X0.14 [PVC]

UL AWM Style	2464/1061
Number of positions	40
Shielded	no
Cable type	40X0.14 [PVC]
Conductor type	Round cable set
Conductor structure signal line	7x 0.16 mm
AWG signal line	26
Conductor cross-section	40x 0.14 mm ²
Wire diameter incl. insulation	1 mm ±0.03 mm
External cable diameter	9.90 mm ±0.4 mm
Outer sheath, material	Semi-rigid PVC
External sheath, color	gray
Conductor material	Tin-plated Cu litz wires
Cable resistance	≤ 145 Ω/km (20 °C)
Insulation resistance	≥ 20 MΩ*km (20 °C)
Smallest bending radius, fixed installation	82 mm
Smallest bending radius, movable installation	155 mm
Dynamic load capacity (bending)	Max. bending cycles: 5000 (at a radius of ≥ 15x outside diameter)
Halogen-free	no
Flame resistance	IEC 60332-1-2 (raw cable) VDE 0842, Part 332-1-2 (raw cable) IEC 60332-3-22 (raw cable) UL VW-1 CSA FT-1
Resistance to oil	can withstand occasional splashes (raw cable)

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

FLK 40/50EZ-DR/ 100/OBC/SLC - Cable



2295509

<https://www.phoenixcontact.com/us/products/2295509>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-5 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
--	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com