

FLK-PVB 2/36 - Termination board



2295664

<https://www.phoenixcontact.com/us/products/2295664>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE module, with two equipotential busbars (P1, P2) for potential distribution, for mounting on NS 35/7.5 or NS 32

Commercial data

Item number	2295664
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	DK2184
GTIN	4017918173715
Weight per piece (including packing)	171.1 g
Weight per piece (excluding packing)	171.1 g
Customs tariff number	85369010
Country of origin	DE

FLK-PVB 2/36 - Termination board



2295664

<https://www.phoenixcontact.com/us/products/2295664>

Technical data

Notes

Type of insulation housing	Polyamide PA non-reinforced
Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.

Product properties

Product type	Potential distributor
Product family	VARIOFACE
Potential connections	Per potential(P1, P2) 2 power/18 distributor terminal blocks

Insulation characteristics

Overvoltage category	III
Pollution degree	2

Electrical properties

Nominal voltage U_N	250 V AC/DC
Max. current carrying capacity per branch	16 A
Max. total current of all branches	30 A (per potential)

Input data

Potential connections	Per potential(P1, P2) 2 power/18 distributor terminal blocks
-----------------------	--

Connection data

Feed-in

Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Number of connections	2
Conductor cross-section rigid	0.2 mm ² ... 6 mm ²
Conductor cross-section flexible	0.2 mm ² ... 4 mm ²
Conductor cross-section AWG	24 ... 10

Distribution

Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Number of connections	36
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12

FLK-PVB 2/36 - Termination board



2295664

<https://www.phoenixcontact.com/us/products/2295664>

Dimensions

Width	96 mm
Height	51.6 mm
Depth	51.7 mm

Material specifications

Color	green (RAL 6021)
-------	------------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Standards and regulations

Standards/regulations	IEC 60664
	DIN EN 50178

Mounting

Mounting type	DIN rail mounting
Mounting position	any

FLK-PVB 2/36 - Termination board



2295664

<https://www.phoenixcontact.com/us/products/2295664>



Drawings

Circuit diagram



FLK-PVB 2/36 - Termination board



2295664

<https://www.phoenixcontact.com/us/products/2295664>

Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com