

DFLK-D15 SUB-HD/B - Termination board



2298069

<https://www.phoenixcontact.com/us/products/2298069>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The VARIOFACE feed-through module implements a 1:1 connection between screw connection terminal blocks and a high-density D-SUB miniature female strip (number of positions: 15). A separate ground pick-off is available.

Commercial data

Item number	2298069
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C429
Product key	DK2AC2
GTIN	4017918207120
Weight per piece (including packing)	73.8 g
Weight per piece (excluding packing)	73.8 g
Customs tariff number	85369010
Country of origin	DE

DFLK-D15 SUB-HD/B - Termination board



2298069

<https://www.phoenixcontact.com/us/products/2298069>

Technical data

Product properties

Product type	Interface module
Product family	VARIOFACE
Number of positions	15

Insulation characteristics: Air clearances and creepage distances

Overvoltage category	II
Pollution degree	2

Electrical properties

Nominal voltage U_N	24 V AC/DC
Max. current carrying capacity per branch	1.5 A

Air clearances and creepage distances

Rated insulation voltage	50 V
--------------------------	------

Connection data

Field level

Connection in acc. with standard	IEC / EN
Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Number of positions	16
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12

Controller level

Connection method	High-density D-SUB socket strip
Number of positions	15

Signaling

Status display present	no
------------------------	----

Dimensions

Item dimensions

Width	39 mm
Height	58.4 mm
Depth	33 mm

Material specifications

Color	green (RAL 6021)
-------	------------------

DFLK-D15 SUB-HD/B - Termination board



2298069

<https://www.phoenixcontact.com/us/products/2298069>

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
---------------------------------	------------------

Standards and regulations

Air clearances and creepage distances

Standards/regulations	DIN EN 50178
-----------------------	--------------

Mounting

Mounting type	Rear mounting
Assembly note	in rows with zero spacing
Mounting position	any

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

DFLK-D15 SUB-HD/B - Termination board



2298069

<https://www.phoenixcontact.com/us/products/2298069>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com