

DFLK-D62 SUBH/S/TP-2,4-0,8 - Termination board



2300876

<https://www.phoenixcontact.com/us/products/2300876>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE feed-through module, for direct coupling of a high-density D-Subminiature pin strip with maxi TERMI-POINT® connectors, number of positions 62

Commercial data

Item number	2300876
Packing unit	10 pc
Minimum order quantity	1 pc
Product key	DK2AC2
GTIN	4017918903220
Weight per piece (including packing)	110.8 g
Weight per piece (excluding packing)	110.8 g
Country of origin	DE

DFLK-D62 SUBH/S/TP-2,4-0,8 - Termination board



2300876

<https://www.phoenixcontact.com/us/products/2300876>

Technical data

Product properties

Product type	Interface module
Product family	VARIOFACE
Number of positions	62

Insulation characteristics: Air clearances and creepage distances

Overvoltage category	II
Pollution degree	2

Electrical properties

Nominal voltage U_N	24 V AC (48 V DC)
Max. current carrying capacity per branch	0.5 A

Air clearances and creepage distances

Rated surge voltage	Basic insulation
---------------------	------------------

Connection data

Field level

Connection method	TERMI-POINT®
Number of positions	64

Controller level

Connection method	D-SUB pin strip
Number of connections	1
Number of positions	62

Signaling

Status display present	no
------------------------	----

Dimensions

Item dimensions

Width	38 mm
Height	180 mm

Material specifications

Color	green (RAL 6021)
Housing insulation material	Polyamide PA non-reinforced

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

DFLK-D62 SUBH/S/TP-2,4-0,8 - Termination board



2300876

<https://www.phoenixcontact.com/us/products/2300876>

Standards and regulations

Air clearances and creepage distances

Standards/regulations	DIN EN 50178
	IEC 60664
	IEC 60664A
	DIN VDE 0110
	DIN VDE 0109-11, draft

Mounting

Mounting type	Rear mounting
Assembly note	in rows with zero spacing
Mounting position	any

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

DFLK-D62 SUBH/S/TP-2,4-0,8 - Termination board



2300876

<https://www.phoenixcontact.com/us/products/2300876>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com