

# DFLK-D62 SUBH/S/TP-2,4-0,8 - Termination board



2300876

<https://www.phoenixcontact.com/us/products/2300876>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE feed-through module, for direct coupling of a high-density D-Subminiature pin strip with maxi TERMI-POINT® connectors, number of positions 62

## Commercial data

Item number	2300876
Packing unit	10 pc
Minimum order quantity	1 pc
Product key	DK2AC2
GTIN	4017918903220
Weight per piece (including packing)	110.8 g
Weight per piece (excluding packing)	110.8 g
Country of origin	DE

# DFLK-D62 SUBH/S/TP-2,4-0,8 - Termination board



2300876

<https://www.phoenixcontact.com/us/products/2300876>

## Technical data

### Product properties

Product type	Interface module
Product family	VARIOFACE
Number of positions	62

#### Insulation characteristics: Air clearances and creepage distances

Overvoltage category	II
Pollution degree	2

### Electrical properties

Nominal voltage $U_N$	24 V AC (48 V DC)
Max. current carrying capacity per branch	0.5 A

#### Air clearances and creepage distances

Rated surge voltage	Basic insulation
---------------------	------------------

### Connection data

#### Field level

Connection method	TERMI-POINT®
Number of positions	64

#### Controller level

Connection method	D-SUB pin strip
Number of connections	1
Number of positions	62

### Signaling

Status display present	no
------------------------	----

### Dimensions

#### Item dimensions

Width	38 mm
Height	180 mm

### Material specifications

Color	green (RAL 6021)
Housing insulation material	Polyamide PA non-reinforced

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

# DFLK-D62 SUBH/S/TP-2,4-0,8 - Termination board



2300876

<https://www.phoenixcontact.com/us/products/2300876>

## Standards and regulations

### Air clearances and creepage distances

Standards/regulations	DIN EN 50178
	IEC 60664
	IEC 60664A
	DIN VDE 0110
	DIN VDE 0109-11, draft

## Mounting

Mounting type	Rear mounting
Assembly note	in rows with zero spacing
Mounting position	any

## Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

# DFLK-D62 SUBH/S/TP-2,4-0,8 - Termination board



2300876

<https://www.phoenixcontact.com/us/products/2300876>

## Environmental product compliance

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)