

FLKM 50/ZFKDS - Termination board



2302955

<https://www.phoenixcontact.com/us/products/2302955>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Standard 1:1 FLK module, with spring-cage connection and flat-ribbon cable connector, no. of positions 50

The figure shows a 40-position version

Commercial data

Item number	2302955
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C422
Product key	DK2181
GTIN	4017918941468
Weight per piece (including packing)	220 g
Weight per piece (excluding packing)	174.96 g
Customs tariff number	85369010
Country of origin	DE

FLKM 50/ZFKDS - Termination board



2302955

<https://www.phoenixcontact.com/us/products/2302955>

Technical data

Product properties

Product type	Interface module
Number of positions	50
No. of channels	2
	4
	6
	8
	16

Insulation characteristics

Insulation	Functional insulation
Overvoltage category	II
Pollution degree	2

Electrical properties

Max. permissible operating voltage	25 V AC
	60 V DC
Max. current carrying capacity per branch	1 A
Rated insulation voltage	63 V
Rated surge voltage	0.6 kV

Connection data

Field level

Connection method	Spring-cage connection
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12

Controller level

Connection method	IDC/FLK pin strip
Number of connections	1
Number of positions	50
Pitch	2.54 mm

Signaling

Status display	no
Status display present	no

Dimensions

Item dimensions

Width	135 mm
Height	77 mm

FLKM 50/ZFKDS - Termination board



2302955

<https://www.phoenixcontact.com/us/products/2302955>

Depth	52.34 mm
-------	----------

Material specifications

Color	green (RAL 6021)
-------	------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Standards and regulations

Standards/regulations	IEC 60664
	DIN EN 50178

Mounting

Mounting type	DIN rail mounting
Mounting position	any

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

FLKM 50/ZFKDS - Termination board


2302955

<https://www.phoenixcontact.com/us/products/2302955>



Drawings

Circuit diagram



FLKM 50/ZFKDS - Termination board



2302955

<https://www.phoenixcontact.com/us/products/2302955>

Classifications

UNSPSC

UNSPSC 21.0	39121432
-------------	----------

FLKM 50/ZFKDS - Termination board



2302955

<https://www.phoenixcontact.com/us/products/2302955>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com