

UMK- D50SUB/M/23CIOC - Termination board



2310727

<https://www.phoenixcontact.com/us/products/2310727>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE module, from a 50-pos. D-SUB pin strip to several blocks of CIOC socket strips, for mounting on NS 32 or on NS 35/7.5

Commercial data

Item number	2310727
Packing unit	1 pc
Minimum order quantity	10 pc
Product key	DK2A82
GTIN	4046356118200
Weight per piece (including packing)	156.6 g
Weight per piece (excluding packing)	148.2 g
Country of origin	DE

2310727

<https://www.phoenixcontact.com/us/products/2310727>

Technical data

Product properties

Product type	Interface module
--------------	------------------

Insulation characteristics

Overvoltage category	II
Pollution degree	2

Electrical properties

Nominal voltage U_N	24 V AC/DC
Max. current carrying capacity per branch	1 A
Max. total current of voltage supply	5 A

Connection data

Controller level

Connection method	D-SUB socket strip
Number of connections	1
Number of positions	50
Connection method	CIOC socket strip

Signaling

Status display	no
Status display present	no

Dimensions

Item dimensions

Width	112.5 mm
Height	77 mm
Depth	39 mm

Material specifications

Color	green (RAL 6021)
Housing insulation material	PVC

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Standards and regulations

Standards/regulations	DIN EN 50178
-----------------------	--------------

UMK- D50SUB/M/23CIOC - Termination board



2310727

<https://www.phoenixcontact.com/us/products/2310727>

Mounting

Mounting type	DIN rail mounting
Assembly note	in rows with zero spacing
Mounting position	any

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

2310727

<https://www.phoenixcontact.com/us/products/2310727>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com