

UM- 8 RELS/KSR-G24/1/SI/N/PLC - Active module



2310811

<https://www.phoenixcontact.com/us/products/2310811>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE output module, with plug-in bases for 8 miniature switching relays, 1 changeover contact each, 5 A fuse each in the output paths, for 24 V DC (without relay), with 9 additional floating connecting terminal blocks

Commercial data

Item number	2310811
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DK2191
GTIN	4046356126212
Weight per piece (including packing)	465 g
Weight per piece (excluding packing)	351.34 g
Country of origin	DE

Technical data

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

Product properties

Product type	Relay Module
No. of channels	8
Compatible components	Miniature switching relay, REL-MR-24DC/21HC
With components	no

Insulation characteristics

Overvoltage category	II
Pollution degree	2

Electrical properties

Rated surge voltage	0.5 kV (Basic insulation)
---------------------	---------------------------

Input data

Nominal input voltage U_N	24 V DC
Input voltage range in reference to U_N	0.8 ... 1.1
Protective circuit	Free running Reverse polarity protection; Polarity protection diode
Operating voltage display	Green LED
Status display/channel	Yellow LED

Output data

Compatible components	Miniature switching relay, REL-MR-24DC/21HC
-----------------------	---

Switching

Contact switching type	1 N/O contact
Maximum switching voltage	24 V AC/DC
Limiting continuous current	5 A

Connection data

Flat-ribbon cable connection

Connection method	Flat-ribbon cable connector in acc. with IEC 60603-13
Number of connections	1
Number of positions	14

PCB connection

Connection method	Screw connection
-------------------	------------------

UM- 8 RELS/KSR-G24/1/SI/N/PLC - Active module



2310811

<https://www.phoenixcontact.com/us/products/2310811>

Stripping length	6 mm
Screw thread	M3
Number of connections	27
Number of positions	9
Conductor cross-section rigid	0.14 mm ² ... 1.5 mm ²
Conductor cross-section flexible	0.14 mm ² ... 1.5 mm ²
Conductor cross-section AWG	26 ... 14

Signaling

Status display present	yes
------------------------	-----

Dimensions

Width	126 mm
Height	128 mm
Depth	76 mm

Material specifications

Color	green (RAL 6021)
Housing insulation material	PVC, side panel PA non-reinforced,

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Standards and regulations

Standards/regulations	DIN EN 50178
-----------------------	--------------

Mounting

Mounting type	DIN rail mounting
Assembly note	in rows with zero spacing
Mounting position	any

2310811

<https://www.phoenixcontact.com/us/products/2310811>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com