

CABLE-40/2FLK16/20,0M/YUC - Front adapter



2321363

<https://www.phoenixcontact.com/us/products/2321363>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cast Yokogawa front adapter with attached round cable and an injection-molded 40-pos. socket strip for the connection of 2 x 8 channels on the field side. Cable length: 20.0 m

Commercial data

Item number	2321363
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C421
Product key	DK222N
GTIN	4046356327435
Weight per piece (including packing)	4 kg
Weight per piece (excluding packing)	4 kg
Customs tariff number	85444290
Country of origin	DE

CABLE-40/2FLK16/20,0M/YUC - Front adapter



2321363

<https://www.phoenixcontact.com/us/products/2321363>

Technical data

Product properties

Product type	Front adapter
--------------	---------------

Electrical properties

Operating voltage (DC)	≤ 30 V DC
Nominal operating mode	100% operating factor
Current (Per path)	≤ 500 mA (uncoiled)

Supported controller: YOKOGAWA CS3000 CentumVP

Suitable I/O card	ADV151
	ADV161

Supported controller: YOKOGAWA STARDOM

Suitable I/O card	NFAI141
	NFAI143

Connection data

Connection 1

Connection in acc. with standard	IEC 60603-13 (in compliance)
Connection method	Yokogawa, I/O cards compatible
Number of connections	1
Number of positions	40
Tightening torque	0.5 Nm (Screw connection)
Insertion/withdrawal cycles	> 50
Pitch	2.54 mm

Connection 2

Connection in acc. with standard	IEC 60603-13 (in compliance)
Connection method	IDC/FLK socket strip
Number of connections	2
Number of positions	16
Insertion/withdrawal cycles	> 50
Pitch	2.54 mm

Dimensions

Cable

Length	20 m
--------	------

Cable/line

40X0.14 [PVC]

UL AWM Style	2464/1061
Number of positions	40

CABLE-40/2FLK16/20,0M/YUC - Front adapter



2321363

<https://www.phoenixcontact.com/us/products/2321363>

Shielded	yes
Cable type	40X0.14 [PVC]
Conductor type	Assembled shielded round cable
Conductor structure signal line	7x 0.16 mm
AWG signal line	26
Conductor cross-section	40x 0.14 mm ²
Wire diameter incl. insulation	1 mm ±0.03 mm
External cable diameter	9.80 mm ±0.3 mm
Outer sheath, material	Semi-rigid PVC
External sheath, color	gray
Conductor material	Tin-plated Cu litz wires
Cable resistance	≤ 145 Ω/km (at 20 °C)
Insulation resistance	≥ 20 MΩ*km (20 °C)
Smallest bending radius, fixed installation	101 mm
Smallest bending radius, movable installation	182 mm
Dynamic load capacity (bending)	Max. bending cycles: 5000 (at a radius of ≥ 18x outside diameter)
Halogen-free	no
Flame resistance	IEC 60332-1-2 (raw cable)
	VDE 0842, Part 332-1-2 (raw cable)
	IEC 60332-3-22 (raw cable)
	UL VW-1
	CSA FT-1
Resistance to oil	can withstand occasional splashes (raw cable)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Degree of protection (Installation location)	≥ IP54 (Installation location)
Ambient temperature (operation) (fixed installation)	-40 °C ... 70 °C (fixed installation)
Ambient temperature (operation) (flexible installation)	-10 °C ... 70 °C (flexible installation)
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	≤ 2000 m

Approvals

UKCA

Certificate	UKCA-compliant
-------------	----------------

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

CABLE-40/2FLK16/20,0M/YUC - Front adapter



2321363

<https://www.phoenixcontact.com/us/products/2321363>

Drawings

Connection diagram

40-pos. connector the I/O card	16-pos. connector to module 1	16-pos. connector to module 2	Wire color
1	2		black
2	1		brown
3	4		red
4	3		orange
5	6		yellow
6	5		green
7	8		blue
8	7		violet
9	10		gray
10	9		white
11	12		white-black
12	11		white-brown
13	14		white-red
14	13		white-orange
15	16		white-yellow
16	15		white-green
17		2	white-blue
18		1	white-violet
19		4	white-gray
20		3	brown-black
21		6	brown-red
22		5	brown-orange
23		8	brown-yellow
24		7	brown-green
25		10	brown-blue
26		9	brown-violet
27		12	brown-gray
28		11	brown-white
29		14	green-black
30		13	green-brown
31		16	green-red
32		15	green-orange
33			green-blue
34			green-violet
35			green-gray
36			green-white
37			yellow-black
38			yellow-brown
39			yellow-red
40			yellow-orange

CABLE-40/2FLK16/20,0M/YUC - Front adapter



2321363

<https://www.phoenixcontact.com/us/products/2321363>

Classifications

ECLASS

ECLASS-13.0

27242292

ETIM

ETIM 9.0

EC002584

UNSPSC

UNSPSC 21.0

32151600

CABLE-40/2FLK16/20,0M/YUC - Front adapter



2321363

<https://www.phoenixcontact.com/us/products/2321363>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com