

VL 19" LCD RTOUCH (S) FPM - Monitor



2400047

<https://www.phoenixcontact.com/us/products/2400047>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

19-inch/48 cm flat panel LCD monitor with resistive touch screen. Includes two rear USB ports



Commercial data

Item number	2400047
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DR12
Product key	DRBABB
GTIN	4046356933100
Weight per piece (including packing)	8.8 kg
Weight per piece (excluding packing)	8.8 kg
Customs tariff number	85299020
Country of origin	TW

VL 19" LCD RTOUCH (S) FPM - Monitor



2400047

<https://www.phoenixcontact.com/us/products/2400047>

Technical data

Notes

Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---------------------------------------------------------------------------

Product properties

Product type	Monitor
--------------	---------

Computer data

Processor	without processor
Operating system	without operating system
RAM	without RAM
Data storage system	without data storage
Cooling	passive
Slots	without slots

Display

Display type	48.3 cm / 19"-TFT
Screen resolution	1280 x 1024 Pixel(s) (SXGA)
Touch technology	analog resistive (polyester)
Display lighting type	LED
Brightness	300 cd/m ² , typical (adjustable)
Color spectrum	16.7 million colors

Electrical properties

Supply

Power supply unit	24 V DC ±20 %
-------------------	---------------

Interfaces

Network	without network
---------	-----------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65 (front), IP20 (back)
Ambient temperature (operation)	0 °C ... 55 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Permissible humidity (storage/transport)	5 % ... 95 %
Shock	15g, 11 ms in accordance with IEC 60068-2-27
Vibration (operation)	DIN EN 60068-2-6

Mounting

Mounting type	Panel cutout
---------------	--------------

VL 19" LCD RTOUCH (S) FPM - Monitor



2400047

<https://www.phoenixcontact.com/us/products/2400047>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
----------------------------------------	----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com