

# SD FLASH 2GB ATWISE - Program/configuration memory



2400088

<https://www.phoenixcontact.com/us/products/2400088>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Program and configuration memory for extending the internal Flash memory, plug-in, 2 GB, with license key for webMI from atwise®

Similar figure

## Product description

Program and configuration memory for storing the application programs and other files in the file system of the PLC, with license for using the webMI functionality from atwise®. The webMI functionality can only be used in conjunction with the atwise Builder 2.5 software and class 1x1 controllers as of firmware 4.30 or the AXC 1050 as of firmware 2.10. Please observe the specified performance data of your controller(s) and check that it/they are suitable for your application. For users who do not wish to use the webMI functionality, the program and configuration memory is also available without a license as an option.

## Your advantages

- License key for webMI from atwise®
- For storing application programs and other files in the file system of the PLC
- Program and configuration memory, plug-in, for webMI from atwise®

## Commercial data

Item number	2400088
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DRAAZA
GTIN	4046356940375
Weight per piece (including packing)	9.2 g
Weight per piece (excluding packing)	8.5 g
Country of origin	DE

# SD FLASH 2GB ATWISE - Program/configuration memory



2400088

<https://www.phoenixcontact.com/us/products/2400088>

## Technical data

### Product properties

Product type	Storage medium
Application	webMI from atwise®
Mounting position	vertical
Memory type	FLASH-EPROM
Memory size	2 GByte

### Electrical properties

Maximum power dissipation for nominal condition	0.165 W
---	---------

#### Supply

Supply voltage	3.3 V DC
Supply voltage range	2.7 V DC ... 3.6 V DC
Typical current consumption	typ. 50 mA

### Material specifications

Housing material	Plastic
------------------	---------

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
---------------------------------	------------------

### Mounting

Mounting position	vertical
-------------------	----------

# SD FLASH 2GB ATWISE - Program/configuration memory



2400088

<https://www.phoenixcontact.com/us/products/2400088>

## Classifications

### UNSPSC

UNSPSC 21.0	32101600
-------------	----------

# SD FLASH 2GB ATWISE - Program/configuration memory



2400088

<https://www.phoenixcontact.com/us/products/2400088>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)