

TP21AM/702000 S00007 - Touch panel



2401015

<https://www.phoenixcontact.com/us/products/2401015>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Touch panel, 14.5 cm / 5.7"-FSTN display (analog resistive (polyester)), 320 x 240 pixel(s) (QVGA), 5 grayscales, Arm9™, 200 MHz, 2x USB Host 2.0, 1 x Ethernet (10/100 Mbps), RJ45, Windows® CE 5.0, Open platform, without bus system.

Commercial data

Item number	2401015
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DRCABA
GTIN	4055626097077
Weight per piece (including packing)	680 g
Weight per piece (excluding packing)	680 g
Country of origin	DE

Technical data

Product properties

Product type	Operator panel
--------------	----------------

Computer data

Processor	Arm9™, 200 MHz
Operating system	Windows® CE 5.0
RAM	64 MB SDRAM
	512 KB SRAM
Data storage system	NOR-Flash, 32 MB

Display

Display type	14.5 cm / 5.7"-FSTN
Screen resolution	320 x 240 Pixel(s) (QVGA)
Touch technology	analog resistive (polyester)
Display lighting type	LED
Brightness	120 cd/m ² typical (adjustable)
MTBF	40000 h
Color spectrum	5 grayscales
Reading angle left	40.00 °
Reading angle right	40.00 °
Reading angle top	45.00 °
Reading angle bottom	45.00 °

Interfaces

Interfaces	2x USB Host 2.0
Optional interfaces	none
Network	1 x Ethernet (10/100 Mbps), RJ45
Bus system	without bus system

System properties

User software	Open platform
---------------	---------------

Electrical properties

Service life of battery	5 years (typical)
-------------------------	-------------------

Supply

Typical current consumption	0.25 A
-----------------------------	--------

Real-time clock

Realtime clock	Yes
----------------	-----

Supply

Power supply unit	24 V DC ±20 %
-------------------	---------------

Mounting

Mounting type	Front mounting
---------------	----------------

Material specifications

Material front plate	Aluminum (natural anodized)
Housing material	Steel sheet, zinc-plated

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65 (front), IP20 (back)
	NEMA 4X
Ambient temperature (operation)	0 °C ... 50 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Altitude	3000 m
Permissible humidity (operation)	20 % ... 85 %
Shock	15g, according to IEC 60068-2-27
Vibration (operation)	1g, according to EN 60068-2-6

Dimensions

External dimensions

Width / Height / Depth	203 mm / 147 mm / 5 mm (Dimensions of the front plate)
------------------------	--

Installation dimensions

Width / Height / Installation depth	195 mm / 139 mm / 66 mm (Mounting cutout, depth with bus if bus system present in the device)
-------------------------------------	---

TP21AM/702000 S00007 - Touch panel



2401015

<https://www.phoenixcontact.com/us/products/2401015>

Classifications

UNSPSC

UNSPSC 21.0	43211904
-------------	----------

2401015

<https://www.phoenixcontact.com/us/products/2401015>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a), 6(a)-I, 6(b), 6(b)-II, 6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-15
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com